

Nubrik Special Shapes Range Technical Data Sheet

BRICKWORKS

| Product Range         | Name                 | Dimension Illustration                                                            | Swatch Image                                                                        | State | Length | Width | Height | Characteristic Unconfined Compressive Strength | Compressive Strength |
|-----------------------|----------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------|--------|-------|--------|------------------------------------------------|----------------------|
| Nubrik Special Shapes | Single Bullnose CB9  |  |  | NSW   | 230    | 110   | 76     | >10                                            | >10                  |
| Nubrik Special Shapes | CB Sill              |  |  | NSW   |        |       | 125    | >10                                            | >10                  |
| Nubrik Special Shapes | Plinth CB6 (LH)      |  |  | NSW   | 230    | 110   | 76     | >10                                            | >10                  |
| Nubrik Special Shapes | Plinth CB7 (RH)      |                                                                                   |  | NSW   | 230    | 110   |        | >10                                            | >10                  |
| Nubrik Special Shapes | Double Bullnose CB10 |                                                                                   |  | NSW   | 230    | 110   | 76     | >10                                            | >10                  |
| Nubrik Special Shapes | Squint CB15          |  |  | NSW   |        | 76    |        | >10                                            | >10                  |
| Nubrik Special Shapes | Reveal CB47          |  |  | NSW   | 230    |       | 76     | >10                                            | >10                  |

This Data represents average results from commercial production lots.

If specific test results are required, sample should be taken from current production lots.

AUSTRALIAN STANDARD TEST METHODS AS/NZS 4456 ARE USED AS APPLICABLE.

Please note: FRL applies up to 3m high - restrained on top and bottom.

NUBRIK